

28 Stem



Description

Ceiling lamp with structure in a black or brass finish. Made with glass spheres lamp holder cavities. Pendants comes in clear or colored glass.

The lamp is created as a result from a complex glass blowing technique whereby air pressure is intermittently introduced into and then removed from a glass matrix which is intermittently heated and then rapidly cooled. The result is a distorted spherical shape with a composed collection of imploded inner shapes, one of which acts as a shade for the light source.

28.12 Stem ceiling mounted requires remote mounted power supplies.

Ø5"5/8 x 1/4" canopy available for remote power supply.

Remote mounted power supplies recommended for ease of long term maintenance.

Installation to be done by certified personnel to ensure code compliance.

LED lamps and power supplies are included.

Optional additional extender available.

28 Stem

Dimensions

- 28.3ss-short) 35"3/8H with 3 pendants.
- 28.3ss-long) 70"7/8H with 3 pendants.
- 28.6ss) 70"7/8H with 6 pendants.
- 28.9ss) 106"1/4H with 9 pendants.
- 28.12ss) 145"5/8H with 12 pendants.

Pendant: 6"1/2 approx.

Additional Extender Lengths:


- 6"
- 12"
- 36"
- 60"

Pendant




± 6"1/2


Ceiling lamp
28.3ss-short




Ceiling lamp
28.3ss-long




Ceiling to floor
28.6ss



Ceiling to floor
28.9ss



Ceiling to floor
28.12ss



Specifications

Mounting: Ceiling mounted.

Glass Color: Clear, colour pendants.

Lamp: 1W LED, 2700K, 100lm.

Finishes: Brass or black powder coated stem.


Materials: Blown glass, brass stem, electrical components.

Power Supply: Integral, except for 28.12 stem.

Bocci recommends remote mounting power supplies for ease of long-term maintenance.

Environment: Indoor, dry location. IP30.


Note: The brass used in our Stem Series is untreated and, as such, will develop a natural patina over time. To avoid any marking or tarnish on the brass during handling and installation, please use the gloves provided in your shipment.



28 Stem

28.3ss-short Compositions

Stem-3A




Stem-3B




28.3ss-long Compositions

Stem-L-3A




Stem-L-3B




28.6ss Compositions

Stem-6A




Stem-6B




28.9ss Compositions

Stem-9A




Stem-9B



28.12ss Compositions

Stem-12A (off)



Stem-12B

